

Elmasonic P 30 SE

Ultrasonic cleaning unit



Elma Order Nos.

Elmasonic P 30 SE (220-240 V)	104 6694
Elmasonic P 30 SE (115-120 V)	104 8321
Basket stainless steel	100 4176
Cover (plastic)	100 3281
Further accessories on request	

The Elmasonic P is the ideal unit for professional applications in analytical and medical laboratories and in industrial production processes. Microprocessor-controlled ultrasonic cleaning with multi-frequency technology (37/80 kHz) and special features are perfect for intensive cleaning tasks and laboratory applications. The units are more powerful than standard ultrasonic cleaning units, and the ultrasonic power can be reduced electronically depending on the cleaning task. The optimized arrangement of the transducer systems on the unit (feasible without drain duct) guarantees the perfect sound field distribution.

Further advantages

- ultrasonic tank made of cavitation-proof stainless steel
- casing made of stainless steel, hygienic and easy to clean
- sandwich-type performance transducer systems
- two ultrasonic frequencies, switchable in one unit: 37 kHz und 80 kHz
 - 37 kHz: for the removal of coarse contaminations and for mixing, dissolving, dispersing and degassing
 - 80 kHz: perfect for the cleaning of capillaries and for the use in quiet work areas, prolonged cleaning period
- automatic frequency switch-over for simultaneous coarse and fine cleaning
- activatable Sweep mode for an optimised sound field distribution within the cleaning bath
- activatable Pulse mode for an intensified ultrasonic cleaning power, additional ultrasonic power up to 20%
- activatable Degas mode for the quick degassing of HPLC samples or solvents and of fresh cleaning liquids
- Auto Degas mode for an automatic degassing cycle, e.g. for fresh cleaning liquids
- ultrasonic power variable for sensitive surfaces
- temperature-controlled ultrasonic operation: ultrasound starts automatically as soon as the preset temperature is reached
- indication of unit settings (e.g. set and actual values) by alphanumeric display
- saving of the last unit settings at switch-off
- electronic turning knobs
- automatic stirring during heating-up process
- pluggable mains cable
- automatic safety switch-off after 12 h operation to prevent unintended permanent operation
- automatic safety switch-off at 90 °C to protect the cleaning items against excess temperatures

Technical data

Mains voltage (Vac)	115-120 V/220-240 V	Weight (kg)	3.3
Ultrasonic frequency (kHz)	37 / 80	Material tank	stainless steel V2A
Power consumption total P 30 H (W)	370 / 350	Material casing	stainless steel V2A
Ultrasonic power effective (W)	120 / 100	Drain	--
Ultrasonic peak performance max.(W)	480 / 400	CE-compliant	√
Heating power (W)	250	Protection class	IP 20
Unit outer dimensions W/D/H (mm)	300 / 179 / 221	Sound pressure level (LpAU) * (dB)	63 / 56
Tank internal dimensions W/D/H (mm)	240 / 137 / 100	Ultrasonic sound level (LpZ) ** (dB)	102 / 99
Basket internal dimensions W/D/H (mm)	198 / 106 / 50		
Max. filling volume tank (lit.)	2.75		

* Sound pressure level measured with basket and cover at a distance of 1 m
 ** Ultrasonic sound level measured with basket and cover at a distance of 1 m